

PRISMATIC PIECES FEEDING MODULE

Mod. MCE-740/EV

Mod. MCE-740/EV is used to distribute prismatic pieces. It has been designed to work with the conveyor module MCE-700/EV. Pieces are expelled by a double-acting cylinder controlled by a 5/2-way electrovalve. The presence of pieces in the column is detected by a microswitch sensor, whereas the position of the cylinder is detected by two magnetic sensors.

The module is assembled on a sectioned aluminium base, and it can be easily moved around the laboratory.

Mod. MCE-740/EV can be fully controlled using a PLC module or an Arduino microprocessor. Thanks to the PLC or Arduino programming software, a wide range of exercises regarding the automation of the module in a working cycle or in stand-alone mode can be developed.

TRAINING PROGRAM

- Fundamentals of Electro-pneumatics
- Piece distribution methods
- Operating an electrovalve
- Operating a set of automated sensors
- Operating a pneumatic cylinder
- PLC control
- Microprocessor control


TECHNICAL SPECIFICATIONS

Modular unit assembled on a sectioned aluminium structure. It includes an I/O interface box with Ø 2 mm terminals that, besides working as control board for the module, enables the students to carry out electrical measurements on its components.

The module can be operated using:

- No. 1 PLC training panel mod. PLC-V8/EV, or
- No. 1 Arduino training panel mod. MPC-18/EV

Power supply (24 Vcc) is provided by the PLC itself or using a MPC-18/EV module.



Sensors and actuators:

- N. 2 Magnetic sensors
- N. 1 Micro-switch
- N. 1 Monostable electrovalve
- N. 1 Microcylinder (piston)

Module inputs and outputs:

- N. 3 Digital inputs
- N. 2 Digital outputs

Dimensions: 160 x 400 x 30 mm

Weight: approx. 3 kg

REQUIRED

UTILITIES (PROVIDED BY THE CUSTOMER)

- Compressed air supply: 5...6 bar

SUPPLIED WITH

THEORETICAL-EXPERIMENTAL HANDBOOK

Presentation of the equipment, experiments, technical specifications with electric and pneumatic diagrams, use and maintenance.

